




BMT Stepper-Controller

2 ports | 0-440 mA

- Two ports to control stepper driven pumps with up to 440 mA
- RPM, PPS and Step-control
- CW and CCW operation
- Up to 1/128 micro steps possible
- Setup of each port can be configured (current, driver-voltage, max. rpm, step sizes, etc.)
- Program linear flow volume using RPM or PPS start and end parameters



Start networking fluidic experiments



Fluidic network

Combine different BMT Controller to a fluidic network using LAN cable or Wi-Fi



Software controlled & programmable

Easily program fluidic operations and control all devices using the BMT PC-Software.



Stand-Alone solution

Start fluidic programs directly at the controller from an USB-Stick.



BMT Fluid Control Solutions GmbH
Maßbornstraße 54f – D-60437 Frankfurt a. M.
Tel.: +49 6101 95400-30 – Fax: +49 6101 95400-39

info@pumpen-ventile.de – www.pumpen-ventile.de

Specifications, etc. may be changed at any time without notice.



2019-10
rev 1.1